

BUEHLER® Delta® PetroCut™ GEOLOGICAL CUTTER

- Affordable, Rugged Manual Cutter Designed for Rocks, Minerals, Nonmetallic and Geological Specimens
- Features Universal Clamping with a Rock Clamp Assembly
- Produces Serial Cuts Quickly and Consistently
- X-Y Table Bed
- Specimen Sizes Up To 3.75" (95mm) in Diameter
- Uses 10" (254mm) Diamond Blade
- Compact Tabletop Design
- Heavy-Duty Aluminum Base
- Large Viewing Window and Lighted Cutting Chamber
- Clean-Out Hose



The Delta® PetroCut™ Geological Cutter is a manual, 4Hp (3.0kW) cutter using a 10" (254mm) Continuous Rim Diamond Blade or Rimlock* Diamond Blade for sectioning of rock, minerals, ceramics, coal, glass, concrete, refractory and many geological samples up to 3.75" (95mm) in size. Features include a Rock Clamp Assembly with an X-Y table bed and cross-feed table for serial cutting. Clamps can be positioned at various points on the table bed. Other specimen vises are available for holding irregular shapes.

The Delta PetroCut Geological Cutter includes a clean-out hose for quick debris removal. Two jets optimize presentation of the coolant to the wheel and specimen. Safety is maintained with an emergency stop, hood lock and a mechanical brake which is engaged when the power is turned off. The heavy duty aluminum cast base provides stability and corrosion resistance. Operation instructions are included.

- 10-2156-260 Delta® PetroCut™**, 230 VAC, 60Hz, 3 Phase
- 10-2156-460 Delta® PetroCut™**, 460 VAC, 60Hz, 3 Phase
- 10-2156-250 Delta® PetroCut™**, 220 VAC, 50Hz, 3 Phase
- 10-2156-400 Delta® PetroCut™**, 380 VAC, 50Hz, 3 Phase

Technical Data

Operation: Manual Chop Cutting

Motor Power: 4.0Hp (3.0kW)

Blade Size and Speed: 10" (254mm) Diameter Blades, 3400 rpm (60Hz), 2830 rpm (50Hz)

Cutting Envelope: Sample Sizes up to 3.75" (95mm)

Controls: Push Button Start and Stop/Emergency Stop; Coolant automatically activates when cutter is started

Other Features: Rock Clamp Assembly, Clean-out Hose, Heavy Duty Interior Lights (14W), Large Viewing Window

Shipping Weight: 200 lbs. (91kg)

Dimensions: 24" W x 17" H x 26.5" D (600mm x 425mm x 665mm)

Accessories

Blade Options**

11-4710 Continuous Rim Diamond Blade (for geological materials - yields best quality cuts) 10" x 0.060" x 1¼" (254mm x 1.5mm x 32mm)

11-4120 Rimlock* Diamond Blade (for geological materials - yields good quality cuts) 10" x 0.040" x 1¼" (254mm x 1.016mm x 32mm)

Optional Accessories

10-2165-260 Recirculating System, 230 VAC, 60Hz, 3 Phase

10-2165-460 Recirculating System, 460 VAC, 60Hz, 3 Phase

10-2165-250 Recirculating System, 220 VAC, 50Hz, 3 Phase

10-2165-400 Recirculating System, 380 VAC, 50Hz, 3 Phase

16-1497 Recirculating System Cart, with Wheels

Vise Accessories

10-3525 Irregular Specimen Speed Vise Kit (Large)

10-3531 Irregular Specimen Speed Vise Kit (Small)

10-3533 Rock Clamp Assembly



Delta® PetroCut™ Cutter showing Rock Clamp Assembly and Clean-out Hose.



Rock Clamp Assembly with specimen.



Optional Speed Vise Accessory Kit allows increased flexibility when clamping irregular shapes.

*Rimlock is a registered trademark of Felker Operations **Blade not included with Delta® PetroCut™

For a complete listing of Buehler Equipment and Consumables, please refer to our Buehler Equipment and Consumables Buyer's Guides. Buehler continuously makes product improvements; therefore, technical specifications are subject to change without notice.

© 2006 BUEHLER LTD. Printed in U.S.A. 25M0106 FN01289 *For metallurgical equipment produced by BUEHLER LTD. USA



BUEHLER
BUEHLER LTD. – Worldwide Headquarters
 41 Waukegan Road • P.O. Box 1
 Lake Bluff, Illinois 60044-1699 USA
 Tel: 847/295-6500 • Fax: 847/295-7979
 Sales: 1/800/BUEHLER • 1/800/283-4537
 Web Site: <http://www.buehler.com>
 Email: info@buehler.com

BUEHLER GMBH - European and MESA Headquarters
 In der Steele 2 • 40599 Düsseldorf
 Postfach 16 03 55 • 40566 Düsseldorf
 Telefon: (49) 211 974100 • Telefax: (49) 211 9741079
 Web Site: <http://www.buehler-met.de>
 Email: info@buehler-met.de

BUEHLER FRANCE
 Téléphone: 0800 89 73 71
 Télécopie: 0800 88 05 27
 Web Site: <http://www.buehler.fr>
 Email: info@buehler.fr

BUEHLER UNITED KINGDOM
 Telephone: 0800 707 6273
 Fax: 0800 707 6274
 Web Site: <http://www.buehler.co.uk>
 Email: sales@buehler.co.uk

BUEHLER CANADA
 10 Carlow Court, Unit #2
 Whitby, Ontario L1N 9T7
 Telephone: (905) 430-4684 • Fax: (905) 430-4647
 Sales Telephone: 1-800-268-3593
 Email: info@buehler.ca

BUEHLER ASIA
 5/F Vogue Centre
 696 Castle Peak Road
 Lai Chi Kok, Kowloon
 Hong Kong, SAR, China
 Telephone: (852) 2307 0909
 Fax: (852) 2307 0233