

# Burst

## Dispensing System

Burst is a flexible, easy to operate dispensing system for all diamond and final polishing suspensions. With a variety of operating modes, solutions can be tailored for any Buehler grinder-polisher set-up.

This product improves both productivity and consistency by dispensing suspensions at fixed intervals and configurable rates.



### Liquid Abrasive Dispensing System

- Increases consistency through automation and repeatability
- Reduces waste & saves time

### Connects up to 5 Modules

- Optional Stadium Seating or Type A USB Connection

### Easy Maintenance

- Easily & quickly replace tubing and pump head

### Compatible with all Grinding-Polishing Systems

- Optional accessories for a wide range of configurations

### Compatible with all Polishing Abrasives

- Magnetically driven stir bar prevents settling of suspensions

### 3 Modes of Operation

- All makes and models in Manual Mode
- In Semi-Automatic Mode with the following Buehler equipment or power heads: AutoMet® 250/300/2000/3000, Vector®, PowerPro™, NelsonZimmer® 2000/3000, MetaServ® 250
- In Automatic Mode with EcoMet® Pro Systems



**BUEHLER**

Excellent Results. Easily Repeatable.™

## STANDARD PRODUCT CONFIGURATIONS & OPTIONS

		Manual	Semi-Automatic	Semi-Automatic with Stadium Seating	Automatic with Stadium Seating*
<b>1 Burst Module</b>	Required	40-10005	40-10005 40-2704	40-10005 40-10004 40-2704	40-10005 40-10004 40-10002
	Optional	40-2823	40-2823	40-10006 40-2822	40-10006
<b>2 Burst Modules</b>	Required	40-10005 (qty. 2) 40-2832	40-10005 (qty. 2) 40-2704 40-2832	40-10005 (qty. 2) 40-10004 40-2704	40-10005 (qty. 2) 40-10004 40-10002
	Optional	40-2822 40-2823	40-2822 40-2823	40-10006 40-2822	40-10006
<b>3 Burst Modules</b>	Required	40-10005 (qty. 3) 40-2832	40-10005 (qty. 3) 40-2704 40-2832	40-10005 (qty. 3) 40-10004 40-2704	40-10005 (qty. 2) 40-10004 40-10002
	Optional	40-2822 40-2823	40-2822 40-2823	40-10006 40-2822	40-10006
<b>4 Burst Modules</b>	Required	40-10005 (qty. 4) 40-2832	40-10005 (qty. 4) 40-2704 40-2832	40-10005 (qty. 4) 40-10004 40-2704	40-10005 (qty. 4) 40-10004 40-10002
	Optional	40-2822 40-2823	40-2822 40-2823	40-10006 40-2822	40-10006
<b>5 Burst Modules</b>	Required	40-10005 (qty. 5) 40-2832 (qty. 2)	40-10005 (qty. 5) 40-2704 40-2832 (qty. 2)	40-10005 (qty. 5) 40-10004 40-2704	40-10005 (qty. 5) 40-10004 40-10002
	Optional	40-2822 40-2823	40-2822 40-2823	40-10006 40-2822	40-10006

\*Compatible only with EcoMet® 250/300 Pro Systems

### Manual Mode

Operates completely independent from the grinder-polisher. The Burst Control Panel is used to start/stop dispensing and to set the suspension volume rate.

### Semi-Automatic Mode

Operates with compatible grinder-polisher via the module-to-grinder-polisher cable. This cable relays the on/off signal from the grinder-polisher. Suspension volume is set on the Control Panel of Burst.

### Automatic Mode

Operates only with the EcoMet® Pro grinder-polishers via the EcoMet® Pro cable. Suspension volume is entered on the EcoMet® Pro touch screen and is dispensed automatically during the polish cycle.

### Power

84-264 VAC, 50/60 Hz, 1 phase

### Weight

Burst Module: 5 lbs [2.26kg]  
Stadium Seating: 10 lbs [4.35kg]

### Dimensions

*Burst Module with Bottle:*

10¼ H x 6 W x 5¼ in D  
[260 x 152 x 133mm]

*Stadium Seating:*

9 H x 6½ W x 24⅝ in D  
[229 x 165 x 625mm]

- 40-10005 Burst Dispensing Module (includes 40-2825 Power Cord)
- 40-10004 Stadium Seating Module
- 40-10006 Dispensing Arm for AutoMet® 250/300
- 40-10002 USB Cable, module to EcoMet® Pro
- 40-2832 USB Cable, module to module (3 pack)
- 40-2704 Cable, module to Grinder-Polisher
- 40-2825 Power Cord, 12V (powers 5 modules)
- 40-2822 Dispensing Stand
- 40-2823 Hand Switch
- 40-2824 Bottle, 16 oz [480mL]
- 00-10099 Replacement Pump
- 00-10100 Stir Bar



The Burst Control Panel is used to start/stop dispensing and to set the suspension volume rates in Manual and Semi-Automatic modes.



The Burst Hand Switch for Manual and Semi-Automatic modes.



**BUEHLER®**, a division of Illinois Tool Works Inc.  
– Worldwide Headquarters  
41 Waukegan Road  
Lake Bluff, Illinois 60044-1699 USA  
Tel: (847) 295-6500 • Fax: (847) 295-7979  
Sales: 1-800-BUEHLER (1-800-283-4537)  
www.buehler.com  
Email: info@buehler.com

**BUEHLER GmbH - European and MESA Headquarters**  
In der Steele 2 • 40599 Düsseldorf  
Telefon: (49) 211 974100 • Telefax: (49) 211 9741079  
www.buehler-met.de  
Email: info@buehler-met.de

**BUEHLER FRANCE**  
Téléphone: 0800 89 73 71  
Télécopie: 0800 88 05 27  
www.buehler.fr  
Email: info@buehler.fr

**BUEHLER UNITED KINGDOM**  
Telephone: 0800 707 6273  
Fax: 0800 707 6274  
www.buehler.co.uk  
Email: sales@buehler.co.uk

**BUEHLER CANADA**  
10 Carlow Court, Unit #2  
Whitby, Ontario L1N 9T7  
Telephone: (905) 430-4684  
Fax: (905) 430-4647  
Sales Telephone: 1-800-268-3593  
Email: info@buehler.ca

**BUEHLER, ASIA-PACIFIC**  
5/F Vogue Centre  
696 Castle Peak Road  
Lai Chi Kok, Kowloon  
Hong Kong, SAR, China  
Telephone: (852) 2307 0909  
Fax: (852) 2307 0233