

HandiMet® 2

Roll Grinder



BUEHLER

Excellent Results. Easily Repeatable.™

The HandiMet® 2 Roll Grinder offers the microstructural analyst an exceptionally convenient and economical instrument for manual grinding applications. The HandiMet® 2 provides a self-contained four-stage grinding station with controlled water flow for lubrication and flushing. Unique water activated clamping holds abrasive papers firmly in position during grinding. No special clamps or hold-downs are required. Continuous water flush removes grinding residue from the abrasive grit. Work surfaces are pitched downward from back to front for operator comfort. For fast, economical, top-quality manual grinding of metallographic samples, specify the new HandiMet® 2 for your laboratory.

Specifications

39-1572 HandiMet® 2 Roll Grinder with four forward pitched $3\frac{7}{16}$ " x $11\frac{1}{2}$ " (9cm x 22cm) dent resistant PVC grinding surfaces, molded RIM housing with stainless steel roll cover and cut-off bar, water activated abrasive paper hold-downs, abrasive roll braking device, stainless steel ball valve for water control, four rolls of CarbiMet® Paper Rolls: Grits 240, 320, 400 and 600 (P280, P400, P800, P1200). Operating instructions.

Dimensions: 19" W x 22" D x 6" H (48cm x 56cm x 15cm)

Shipping Weight: 33 lbs. (15kg)

Abrasive Rolls

30-5143-240-001 CarbiMet® Paper Rolls, 240 (P280) grit, $3\frac{7}{16}$ " x 75' (8.8cm x 23m), 1 roll per package.

30-5143-320-001 CarbiMet® Paper Rolls, 320 (P400) grit, $3\frac{7}{16}$ " x 75' (8.8cm x 23m), 1 roll per package.

30-5143-400-001 CarbiMet® Paper Rolls, 400 (P800) grit, $3\frac{7}{16}$ " x 75' (8.8cm x 23m), 1 roll per package.

30-5143-600-001 CarbiMet® Paper Rolls, 600 (P1200) grit, $3\frac{7}{16}$ " x 75' (8.8cm x 23m), 1 roll per package.



Covered storage area for abrasive rolls provides protection and permits rapid changing of grinding surfaces when required.



The HandiMet® 3 provides a compact, self-contained, four-stage grinding station to accommodate a variety of sample preparation applications.



Abrasive rolls are available in a variety of grits.

For a complete listing of consumables, please refer to our Consumables Buyer's Guide. Buehler continuously makes product improvements; therefore, technical specifications are subject to change without notice.

BUEHLER ANALYST® SECTION 4



BUEHLER®, a division of Illinois Tool Works Inc.
– Worldwide Headquarters
 41 Waukegan Road
 Lake Bluff, Illinois 60044-1699 USA
 Tel: (847) 295-6500 • Fax: (847) 295-7979
 Sales: 1-800-BUEHLER (1-800-283-4537)
 www.buehler.com
 Email: info@buehler.com

BUEHLER GmbH - European and MESA Headquarters
 In der Steele 2 • 40599 Düsseldorf
 Telefon: (49) 211 974100 • Telefax: (49) 211 9741079
 www.buehler-met.de
 Email: info@buehler-met.de

BUEHLER FRANCE
 Téléphone: 0800 89 73 71
 Télécopie: 0800 88 05 27
 www.buehler.fr
 Email: info@buehler.fr

BUEHLER UNITED KINGDOM
 Telephone: 0800 707 6273
 Fax: 0800 707 6274
 www.buehler.co.uk
 Email: sales@buehler.co.uk

BUEHLER CANADA
 10 Carlow Court, Unit #2
 Whitby, Ontario L1N 9T7
 Telephone: (905) 430-4684
 Fax: (905) 430-4647
 Sales Telephone: 1-800-268-3593
 Email: info@buehler.ca

BUEHLER, ASIA-PACIFIC
 5/F Vogue Centre
 696 Castle Peak Road
 Lai Chi Kok, Kowloon
 Hong Kong, SAR, China
 Telephone: (852) 2307 0909
 Fax: (852) 2307 0233